

## Integrated Cellular Blind PRACTICAL SYSTEM

Practical System is a manually-operated magnetic system with raising and lowering functions for cellular blinds encapsulated within 24mm cavity double glazing units.

The system is operated by a magnetic slider, placed on the right or left edge of the glass. A narrow adhesive profile ensures the linear movement of the slider. The blind is raised and lowered by moving the slider up or down.

Provides much faster raising & lowering without any need for a chain or cord.

Blind moves 1,9 meter when the button is moved for a meter.

Since it can completely obscure the room, due to its black-out feature, it is preferred where higher daylight control is desired.

Since it's a double-sided fabric with a honeycomb shape, no cords or holes are visible. Only the fabric itself is visible.


The system can be supplied either with warm edge or aluminum spacer bars according to demand.

The position of the cellular blind between insulated double glazing prevents any physical intervention. It also ensures that the blind is not dusted, contaminated, or affected by weather conditions. Thus, it does not require any maintenance and cleaning.

Suitable for every type of window frame.



## FEASIBILITY CHARTS



### Possible Dimensions

W min = 250 mm \*      W max = 1000 mm \*\*  
H min = 600 mm \*\*\*      H max = 2600 mm

\* When the width is less than 350 mm, the height shall not exceed 1300 mm

\*\* According to height, width can go up to 1400 mm

\*\*\* According to width, height can be less than 600 mm